



54EB43FC Rotary Limit Switch 72:1 Long Dwell Cam

By Gleason Reel
Catalog # [54EB43FC](#)

Rotary Limit Switch 72:1 Long Dwell Cam



Features

- Standard, Long Dwell or Fine Adjustment Cams
- Easy to Wire and Adjust
- Rugged Die-cast Aluminum Housing
- Operating temperature range is -20F to +150F
- Humidity up to 90% is acceptable
- Ambient pressure of -0.5 to +2.0 psig is acceptable (where 0 psig equals 14.7 psi atmospheric)

General

| | |
|------------------|---|
| Application | Designed to serve as pilot controls for magnetic reversing starters and contactors which in turn make and break full voltage between line and load. |
| Catalog Number | 54EB43FC |
| Product Category | Limit Switches |
| Series | 54 |
| UPC | 783246012753 |

Dimensions

| | |
|-----------------------------|-----|
| Circuits Normally Closed | 4 |
| Circuits Normally Open | 4 |
| Maximum Shaft Turns To Trip | 60 |
| Contacts | |
| Minimum Shaft Turns To Trip | 2 |
| Contacts | |
| Over Travel Shaft Turns | 10 |
| Reset Shaft Turns | 1.5 |

Certifications And Compliance

Nema Rating 1, 12

Product Assets

[Brochures - Series 54 Rotary Limit Switches](#)
[Brochures - Pre-Engineered Products - Reels, Cable Track and Festoons, Controls, Automation Components](#)
[Engineering Drawing - Series 54 Rotary Limit Switch DXF](#)
[Engineering Drawing - Series 54 Rotary Limit Switch DWG](#)
[Installation Manuals - Limit Switch-Series 54 "Standard Adjustment" Maintenance Instructions 626382](#)



A Hubbell brand