



C60-F03-2005E-Z C60 End Clamp

By Gleason Reel
Catalog # C60-F03-2005E-Z

C60 End Clamp



Features

- Flat Clamp design
- Hardware is Zinc Plated
- 1.57" Dia Precision ball bearing steel wheels
- Max Trolley load =125Lbs
- Travel speed up to 450 fpm
- Max travel = 500ft

General

Accessories

- Cable Clamps - Flat Design
- Junction Box(es)
- Cable - Round Or Flat
- Terminal Blocks
- Ty-Wraps
- Hose - General Purpose Or Hydraulic
- Tow Chains
- Cable Glands For Single Cables Or Groups

Cable Type

Flat

Catalog Number	C60-F03-2005E-Z
Clamping Element Design	Flat Clamp
Finish Type	Orange Baked Polyester Powder Finish
Material - Hardware	Zinc Plated Hardware
Series	C60
Type	End Clamp

Dimensions

Bolt Hole Spacing - Top Terminal	3.5
Diameter - Saddle	3.12
Height - Window	2 in
Overall Length	6.69
Radius - Saddle	1.56
Width - Window	5 in

Product Assets

[Installation Manuals - C-Rail Festoon Installation Instructions 043574](#)
[Specifications - C60F032005EZ](#)



A Hubbell brand