

Corridor Surface-Mount VoIP Telephone (Auto-dial)

By GAI-Tronics
Catalog # 210-712

GAI-Tronics ADA-compliant corridor telephone with 29" handset cord, surface mount, signed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The telephones are programmed to automatically dial when the handset is taken off-hook (number/address programming via imbedded web browser). The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet SIP network and operate using power-over-Ethernet or an alternative power source.



General

Application	Corridor Installation, ADA compliant
Color	Silver
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Auto-Dial
Weather Rating	Indoor

Dimensions

Cubic Capacity	58.81095 cu.in
Depth	3.27 in
Dimensions	10.0 in x 5.5 in x 3.27 in
Height	3.27 in
Length	10 in
Weight	5.5 lb
Width	5.5 in

Electrical Ratings

Signal	Ethernet
Voltage Rating	24-48 VDC or PoE V
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15
Nema Rating	IP66

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
[Installation Manuals - Rugged VoIP Handset Telephones](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-210712-SPEC-EN | REV 6/2024