

Tough Phone - Analog (Keypad)

By GAI-Tronics
Catalog # 226-001

The Tough Phone series was developed for public and industrial areas requiring a virtually indestructible telephone. Housed in a 1/4-inch thick, sand-cast aluminum, weatherproof enclosure and coated with an exterior polyurethane finish.



Features

- Cast Aluminum Enclosure with Polyurethane Finish
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and 15-inch Armored Cord
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed

General

Application	Industrial Areas Public Areas
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	74 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
Weather Rating	NEMA 3R

Dimensions

Dimensions	6.15 in x 9.7 in x 13.5 in
Height	13.5 in
Length	6.15 in
Weight	18 lb
Width	9.7 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

Certified Listed UL/CSA, FCC, IC

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Rugged Analog Telephones with Keypads](#)
[Literature - Rugged Telephones - Keypad](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-226001-SPEC-EN | REV 6/2024