

# Indoor Rugged Telephone - Analog/SMART (Keypad)

By GAI-Tronics  
Catalog # 246-005

This indoor series telephone is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) HytreI® handset cord. SMART models include the ability to be centrally monitored for health status via our TMA software.



## Features

- Telephone Line Powered
- No External Power Needed
- Braille Metallic Keypad
- Handset with Noise-canceling Microphone and HytreI® Coiled Cord (6-ft extended)
- Hearing Aid Compatible Handset
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Dual Output Control
- Conformal Coated PCBA
- Three Number Rollover - Unit Dials up to Three Different Numbers to Ensure
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

## General

Application	Indoor Use
Color	Gray
Connectivity Options	Analog/SMART
Mount location	Surface-Mount
Output Level Ringer	90 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
Weather Rating	Indoor

## Dimensions

Dimensions	6.9 in x 8 in x 9.5 in
Height	9.5 in
Length	6.9 in
Weight	4.8 lb
Width	8 in

## Electrical Ratings

Signal	Phone Line
--------	------------

## Certifications And Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

## Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Telephone Management Application Installation Bulletin](#)
- [Installation Manuals - SMART Handset Telephones with Keypads \(Model 226-005, 246-005, 256-005, and 276-005\)](#)
- [Installation Manuals - Telephone Management Application \(TMA\) User Guide](#)
- [Literature - Telephone Management Application \(TMA\)](#)
- [Literature - SMART Rugged Telephones - Keypad](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
GTC-246005-SPEC-EN | REV 6/2024