

Outdoor Rugged Telephone - Analog (Keypad)

By GAI-Tronics
Catalog # 256-001

This outdoor series telephone includes a latching door and is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord.



Features

- High-impact, Non-metallic Enclosure
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Surface-mount
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and Hytrel® Coiled Cord (6-ft extended)
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Ring-relay Kit Available
- Conformal-coated PCBA
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed

Application

Outdoor Use

General

Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	84 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
UPC	850025795104
Weather Rating	NEMA 3R

Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Height	13.2 in
Length	7.4 in
Weight	8.2 lb
Width	9.4 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications and Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Rugged Analog Telephones with Keypads](#)
[Literature - Rugged Telephones - Keypad](#)

Related Products

[230-001 - Pole Mounting Kit \(for 25x, 351, 354, XB001\)](#)