

Clean Phone® VoIP Telephone, 14 Button, Surface-Mount, CE certified RoHS compliant

By GAI-Tronics
Catalog # 116-02-0418-01W



The Clean Phone® telephone offers hands-free communications over an existing VoIP network for clean room environments. These telephones are intended for connection via RJ45 to a 10/100 BaseT Ethernet and operate using either PoE or an external dc power source. The Clean Phone® VoIP telephone features alarm reporting that enables system supervisors to monitor the telephone’s activity and address maintenance issues immediately. The Clean Phone® telephone is also compatible with GAI-TRONICS’ [TMA \(Telephone Management Application\)](#) software for maintenance monitoring from a central location. Embedded web pages permit access to each telephone, via a browser such as Internet Explorer®, to view, monitor, and change settings within the unit.

General

Application	Clean Rooms Clinical Environments Sterile Environments Sanitary Environments
CE Compliant	CE certified RoHS compliant, Sterile Area
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-20° C to +60° C
Storage Temperature Range	-40° C to +70° C
Type	Keypad

Certifications And Compliance

CE Compliant	CE certified RoHS compliant, Sterile Area
--------------	--

Product Assets

- [Certifications - EU Declaration of Conformity \[Help Point VoIP Telephones\]](#)
- [Installation Manuals - VoIP Clean Phone® Telephones \(1193 Version\)](#)