

Flush-panel Handset Telephone - Analog/SMART (Keypad)

By GAI-Tronics
Catalog # [276-005](#)

The 27x series handset telephone is designed to flush or surface mount (using 236 series enclosure). This unit has a brushed stainless steel faceplate with a metallic non-moveable hookswitch. Standard equipment also includes a 29-inch lanyard armored cord and tamper resistant hardware. SMART models include the ability to be centrally monitored for health status via our TMA software.



Features

- Stainless Steel Construction
- Telephone Line Powered
- No External Power Needed
- Braille Metallic Keypad
- Handset with Noise-canceling Microphone and 29-inch Armored Cord
- Hearing Aid Compatible Handset
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Conformal-coated PCBA
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Dual Output Control
- Three Number Rollover - Unit Dials up to Three Different Numbers to Ensure
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

General

Application	Indoor & Outdoor Use
Color	Silver
Connectivity Options	Analog/SMART
Mount location	Flush-Mount
Output Level Ringer	86 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
Weather Rating	Type 3R

Dimensions

Dimensions	2.44 in x 10.0 in x 12.0 in
Height	12 in
Length	2.44 in
Weight	7 lb
Width	10 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Telephone Management Application Installation Bulletin](#)
- [Installation Manuals - SMART Handset Telephones with Keypads \(Model 226-005, 246-005, 256-005, and 276-005\)](#)
- [Installation Manuals - Telephone Management Application \(TMA\) User Guide](#)
- [Literature - Telephone Management Application \(TMA\)](#)
- [Literature - SMART Rugged Telephones - Keypad](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-276005-SPEC-EN | REV 6/2024