

Hazardous Area Analog Telephones - Indoor - Div. 2

By GAI-Tronics
Catalog # 341-001

Our indoor model 341-001, provides fully-functional, line-powered communications that are approved for use in Class I, Division 2, Groups A, B, C, D; Class II, Division 2, Groups F and G; Class III classified areas. The coiled handset cord on the non-metallic model is molded of thermoplastic elastomer to provide outstanding performance, memory, and long life.



Features

- Hazardous Area approved for: Class I, Division 2, Groups A, B, C, D; Class II, Division 2, Groups F and G; Class III
- Economical Communications for Division 2 Areas
- Indoor and Outdoor Models
- Anti-corrosive Enclosures
- Hearing Aid Compatible (HAC) with Pushbutton Volume Control
- Hytrel Coiled Cord or Straight Armored Cord
- Sealed Chrome-plated Keypad
- Extreme Operating Temperature Range
- Conformal Coating on PCBA

General

Color	Blue
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	92 dBA @ 2 ft.
Signal Type	Analog
Type	Indoor Use
Weather Rating	Indoor

Dimensions

Dimensions	6.9 in x 8 in x 9.5 in
Height	9.5 in
Length	6.9 in
Weight	6 lb
Width	8 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

Certification	UL CSA IC
Hazardous Rating(s)	Class I, Division 2, Groups A, B, C, D Class II, Division 2, Groups F & G Class III, Division 2

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Model 226-002, 341-001, and 351-001 Div. 2 Industrial Telephones](#)
[Literature - Hazardous Area Telephones](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-341001-SPEC-EN | REV 6/2024