

Indoor / Outdoor Compression Driver - 13314 Series (100V)

By GAI-Tronics
Catalog # [13314-004](#)

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.

Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

General

Catalog Number	13314-004
Operating Temperature	-40° C to +70° C (-40° F to +158° F)

Dimensions

Weight	4.3 lb
--------	--------

Electrical Ratings



Impedance	100V
-----------	------

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Div. 2, Groups A, B, C, D• Class II, Div. 2, Groups F, G• Class III, Div. 2
Nema Rating	4X

Product Assets

- [Installation Manuals - Model 13314-004 Div. 2 Hazardous Area 100-Volt Horn Driver](#)
- [Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
- [Literature - Indoor / Outdoor Compression Driver](#)
- [Specifications - 13314004](#)