



Integral Loudspeaker - Model 13350

By GAI-Tronics
Catalog # 13350

GAI-Tronics revolutionary Model 13350 Integral Loudspeakers provide all-purpose paging in a compact size. These truly weatherproof outdoor loudspeakers are suited for commercial as well as industrial applications. Other speakers may be rain-tight, but only the 13350 can withstand a direct hosedown without impaired performance.



Features

- 12 Watt, 8 Ohm
- 90 Degree Nominal Dispersion Angle
- Waterproof
- Highly Resistant to Chemicals & Corrosives
- Increased Intelligibility
- Durable, Glass-Reinforced Polyester, Black
- Integrated Mounting Holes, Conduit Entries & Electrical Connections
- Reversible Rear Enclosure

General

Operating Temperature	<ul style="list-style-type: none">• -40°C to +70 °C• -40°F to 158 °F
Power	16 Watt Continuous
UPC	850025795166

Dimensions

Cubic Capacity	619.965248 cu.in
Depth	8.12
Height	9.52 in
Weight	6.4 lb
Width	8.02 in

Product Assets

[Brochures - Loudspeaker Selection Guide](#)
[Installation Manuals - Model 13350 and 13351 Integral Loudspeakers](#)
[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
[Literature - Integral Loudspeaker](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-13350-SPEC-EN | REV 7/2023