

# Analog UL Class I Div 1 Telephone

By GAI-Tronics  
Catalog # 352-001



GAI-Tronics introduces the world's first UL Class I Division 1 telephone and is available in standard analog. This rugged analog handset is UL approved to Class I Division 1 Groups B, C, & D, Class II Groups F & G and Class III, Type 4X, and ABS Type Approved. Analog variants are available with relay contact. Ring relay contacts are 5A, 250 V ac / 30 V dc rated.

## General

Catalog Number	352-001
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	External required
Signal Type	Analog
Weather Rating	Type 4X

## Dimensions

Cubic Capacity	1175.265 cu.in
Depth	9.36
Height	12.25 in
Weight	28 lb
Width	10.25 in

## Electrical Ratings

Signal	Phone Line
--------	------------

## Certifications And Compliance

Certification	UL cUL
Compliance	Telecoms Compliance to Standards: FCC CFR 47 Part 15
Hazardous Rating(s)	Class I, Division 1, Groups B, C, & D  Class II, Division 1, Groups F & G  Class III, Division 1

## Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Installation Manuals - Division 1 Telephones \(Model 352-001, 352-002, 352-003, and 352-004\)](#)  
[Literature - UL Class I Division 1 Telephones \(VoIP / SMART / Analog\)](#)



A Hubbell brand