

Integral Loudspeaker - Model 13351

By GAI-Tronics
Catalog # 13351

GAI-Tronics revolutionary Model 13351 Integral Loudspeakers provide all-purpose paging in a compact size. These truly weatherproof outdoor loudspeakers are suited for commercial as well as industrial applications. Other speakers may be rain-tight, but only the 13351 can withstand a direct hosedown without impaired performance.



Features

- 12 Watt, 70 V
- 90 Degree Nominal Dispersion Angle
- Waterproof
- Highly Resistant to Chemicals & Corrosives
- Increased Intelligibility
- Durable, Glass-Reinforced Polyester, Black
- Integrated Mounting Holes, Conduit Entries & Electrical Connections
- Reversible Rear Enclosure

General

Operating Temperature	-40°C to +70 °C -40°F to 158 °F
Power	16 Watt Continuous

Dimensions

Cubic Capacity	619.965248 cu.in
Depth	8.12
Height	9.52 in
Weight	7.5 lb
Width	8.02 in

Product Assets

- [Brochures - Loudspeaker Selection Guide](#)
- [Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
- [Installation Manuals - Model 13350 and 13351 Integral Loudspeakers](#)
- [Literature - Integral Loudspeaker](#)