



## Tough Phone - Analog/SMART (Auto-dial)

By GAI-Tronics  
Catalog # 227-005

The Tough Phone series was developed for public and industrial areas requiring a virtually indestructible telephone. Housed in a 1/4-inch thick, sand-cast aluminum, weatherproof enclosure and coated with an exterior polyurethane finish. SMART Models include the ability to be centrally monitored for health status via our TMA software.



### Features

- Cast Aluminum Enclosure with Polyurethane Finish
- Telephone Line Powered
- No External Power Needed
- Auto Dials up to 31 Digits
- Handset with Noise-canceling Microphone and 15-inch Armored Cord
- Hearing Aid Compatible
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Surface-mount
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Conformal-coated PCBA
- Dual Output Control
- Three Number Rollover - Unit Dials Up to Three Different Numbers to Ensure Emergency Calls are Answered
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

### General

Color	Gray
Connectivity Options	Analog/SMART
Mount location	Surface-Mount
Output Level Ringer	75 dBA @ 2 ft.
Signal Type	Analog
Type	Public & Industrial Areas
Weather Rating	NEMA 3R

### Dimensions

Dimensions	6.1 in x 9.7 in x 13.5 in
Height	13.5 in
Length	6.1 in
Weight	18 lb
Width	9.7 in

### Electrical Ratings

Signal	Phone Line
--------	------------

### Certifications and Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

### Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Installation Manuals - Telephone Management Application Installation Bulletin](#)  
[Installation Manuals - SMART Auto-Dial Handset Telephones Model 227-005, 247-005, 257-005, and 277-005](#)  
[Installation Manuals - Telephone Management Application \(TMA\) User Guide](#)  
[Literature - SMART Rugged Telephones - Auto-dial](#)  
[Literature - Telephone Management Application \(TMA\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
GTC-227-005-SPEC-EN | REV 7/2023