

RED ALERT® WiFi VoIP Emergency Telephones - Model 397-810A

By GAI-Tronics
 Catalog # 397-810A

These WiFi VoIP Flush-Mount Telephones are designed to provide direct point-to-point communications between personnel over an existing wireless local area network (WLAN), meeting IEEE 802.11 b/g standards. These telephones will operate from an external dc power source which is the only wiring required for operation.



General

Application	Emerg. Telephone Comm., wireless (campuses, parking lots, paths)
Color	Silver
Connectivity Options	WiFi VoIP
Construction	Front Panel: 14-Gauge Type 304 Brushed Stainless Steel; Dust Cover: 16-Gauge Cold-Rolled Steel With Black Polyurethane Finish
Mount location	Flush-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Emergency Telephones
	HELP Button
Weather Rating	Type 3R

Dimensions

Dimensions	2.38 in x 10.0 in x 12.0 in
Height	12 in
Length	2.38 in
Weight	7.2 lb
Width	10 in

Electrical Ratings

Signal	WiFi
Voltage Rating Description	24-48 VDC

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Installation Manuals - RED ALERT® Hands-free WiFi VoIP Telephone Manual](#)
- [Literature - WiFi VoIP Hands-free Telephones - Flush-mount](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-397810A-SPEC-EN | REV 6/2024