



120 V Cellular GSM Tower Assembly

By GAI-Tronics
Catalog # [234-500GSM](#)

Free-standing tower, GSM cellular; including lens cover kit, antenna kit, LED panel light, GSM subpanel, battery kit; 120 V ac.



Features

- Architectural Bronze color is aesthetically pleasing in all settings
- “EMERGENCY” lettering on all sides for high visibility
- Custom colors and graphics available
- UL Listed
- Accommodates GAI-TRONICS’ LED Strobe and flush-mount emergency telephones (each sold separately)
- Wind Speed Rated @ 140 MPH* (*Reference AASHTO LTS6 Risk Category II; International Building Code)
- ADA Compliant

General

Compatibility	GAI-TRONICS’ Telephones and Strobes are Sold Separately. Model 234 Series Tower is not compatible with RED ALERT® surface-mount or retrofit telephones.
Finish Type	Powder-Coated Epoxy
Material	Steel
Type	Cellular Tower
Weather Rating	UL/cUL listed Outdoor Telephone Tower

Dimensions

Cubic Capacity	11400 cu.in
Depth	10 in
Height	114 in
Width	10 in

Certifications and Compliance

Certified Listed	UL/cUL
------------------	--------

Product Assets

[Brochures - Emergency Communications Tower Applications \(Solar/Wireless/Surveillance\)](#)
[Brochures - Red Alert Telephone Brochure](#)

Related Products

[540-001 - LED Strobe, 120 V ac](#)
[541-001 - Low Voltage LED Strobe, 12-24 V dc](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
GTC-234-500GSM-SPEC-EN | REV 7/2023