

Indoor Rugged Telephone - Analog (Keypad)

By GAI-Tronics
Catalog # 246-001

This Indoor Analog Telephone is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) HytreI® handset cord.



Features

- High-impact, Non-metallic Enclosure
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and HytreI® Coil Cord (6-ft extended)
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- FCC & IC Certified, UL60950 Listed

General

Application	Indoor Use
Catalog Number	246-001
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	92 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
Weather Rating	Indoor

Dimensions

Dimensions	6.9 in x 8 in x 9.5 in
Height	9.5 in
Length	6.9 in
Weight	6 lb
Width	8 in

Electrical Ratings

Signal	Phone Line
--------	------------

Certifications And Compliance

Certified Listed UL/CSA, FCC, IC

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Rugged Analog Telephones with Keypads](#)
[Literature - Rugged Telephones - Keypad](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-246001-SPEC-EN | REV 6/2024