

Indoor Rugged Telephone - Analog (Auto-dial)

By GAI-Tronics
Catalog # [247-001](#)

GAI-Tronics' Indoor Analog Telephone is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord.

Features

- High-impact, Non-metallic Enclosure
- Extended Temperature Range: - 40°F to +140°F
- Auto Dials up to 31 Digits
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and Hytrel® Coil Cord (6-ft extended)
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- FCC & IC Certified, UL60950 Listed

Application

Indoor Use

General

| | |
|----------------------|-----------------|
| Catalog Number | 247-001 |
| Color | Gray |
| Connectivity Options | Analog |
| Mount location | Surface-Mount |
| Output Level Ringer | 92 dBA @ 2 ft. |
| Signal Type | Analog |
| Specifications | UL/CSA, FCC, IC |



| | |
|----------------|-----------|
| Type | Auto-Dial |
| Weather Rating | Indoor |

Dimensions

| | |
|-----------------------|------------------------|
| Dimensions | 6.9 in x 8 in x 9.5 in |
| Dimensions - Shipping | 13.0 x 12.0 x 8.0 |
| Height | 9.5 in |
| Length | 6.9 in |
| Weight | 6 lb |
| Width | 8 in |

Electrical Ratings

| | |
|---------------|------------|
| Input Voltage | Phone Line |
| Signal | Phone Line |

Certifications And Compliance

| | |
|------------------|-----------------|
| Certified Listed | UL/CSA, FCC, IC |
|------------------|-----------------|

Product Assets

- [Brochures - Rugged Telephone Brochure](#)
- [Installation Manuals - Rugged Analog Auto-Dial Telephones](#)
- [Literature - Rugged Telephones - Auto-dial](#)
- [Specifications - 247001](#)