

Outdoor Rugged Telephone - Analog (Auto-dial)

By GAI-Tronics
Catalog # 257-001

This outdoor series telephone includes a latching door and is constructed of a high-impact, non-metallic enclosure with an industrial strength, six-foot (extended) Hytrel® handset cord.



Features

- High-impact, Non-metallic Enclosure
- Extended Temperature Range: - 40°F to +140°F
- Auto Dials up to 31 Digits
- Surface-mount
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-canceling Microphone and Hytrel® Coiled Cord (6-ft extended)
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Ring-relay Kit Available
- Conformal-coated PCBA
- NEMA 3R Weatherproof Rating
- FCC & IC Certified, UL60950 Listed

General

Application	Outdoor Use
Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	84dBA @ 2 ft.
Signal Type	Analog
Type	Auto-Dial

Dimensions

Dimensions	7.4 in x 9.4 in x 13.2 in
Height	13.2 in
Length	7.4 in
Weight	10 lb
Width	9.4 in

Certifications And Compliance

Certified Listed UL/CSA, FCC, IC

Product Assets

[Brochures - Rugged Telephone Brochure](#)
[Installation Manuals - Rugged Analog Auto-Dial Telephones](#)
[Literature - Rugged Telephones - Auto-dial](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-257001-SPEC-EN | REV 6/2024