

## Flush-panel Handset Telephone - Analog (Keypad)

By GAI-Tronics  
Catalog # [276-001](#)

The 27x series handset telephone is designed to flush or surface mount (using 236 series or 238 enclosure). This unit has a brushed stainless steel faceplate with a metallic non-moveable hookswitch. Standard equipment also includes a 29-inch lanyard armored cord and tamper resistant hardware.



### Features

- Stainless Steel Construction
- Extended Temperature Range: - 40°F to +140°F
- Braille Metallic Keypad
- Hearing Aid Compatible
- Non-movable Hookswitch
- Volume Control Handset with Noise-cancelling Microphone and 29-inch Armored Cord
- Non-volatile Electronic Memory (Stand-by Batteries Not Required)
- Conformal-coated PCBA
- FCC & IC Certified, UL60950 Listed
- NEMA 3R Weatherproof Rated

### Application

Indoor & Outdoor Use

### General

Color	Silver
Connectivity Options	Analog
Mount location	Flush-Mount
Output Level Ringer	86 dBA @ 2 ft.
Signal Type	Analog
Type	Keypad
Weather Rating	Type 3R

### Dimensions

Dimensions	2.51 in x 10.0 in x 12.0 in
Height	12.0 in
Length	2.51 in
Weight	6.5 lb
Width	10.0 in

### Electrical Ratings

Signal	Phone Line
--------	------------

### Certifications and Compliance

Certified Listed	UL/CSA, FCC, IC
------------------	-----------------

### Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Installation Manuals - Rugged Analog Telephones with Keypads](#)  
[Literature - Rugged Telephones - Keypad](#)