

## Flush-panel Telephone - Analog/SMART (Auto-dial)

By GAI-Tronics  
Catalog # [277-005](#)

The 27x series telephone is designed to flush or surface mount (using 236 series enclosure). This unit has a brushed stainless steel faceplate with a metallic non-moveable hookswitch. Standard equipment also includes a 29-inch lanyard armored cord and tamper resistant hardware. SMART models include the ability to be centrally monitored for health status via our TMA software.



### Features

- Stainless Steel Construction
- Extended Temperature Range: - 40°F to +140°F
- Auto-dial or Ring-down Operatio
- Handset with Noise-canceling Microphone and 29-inch Armored Cord
- Hearing Aid Compatible Handset
- Volume Control Push Button (Front Panel)
- Non-movable Hookswitch
- Conformal-coated PCBA
- Remote Programming
- Phone's Health Status Reported to Central P.C.
- Programmable Polling or Call-in Scheduling
- Dual Output Control
- Three Number Rollover - Unit Dials up to Three Different Numbers to Ensure
- Emergency Calls are Answered
- FCC & IC Certified, UL60950 Listed
- TMA Compatible

### Application

Indoor & Outdoor Use

### General

Color	Silver
Connectivity Options	Analog/SMART
Mount location	Flush-Mount
Output Level Ringer	86 dBA @ 2 ft.
Signal Type	Analog
Type	Auto-Dial
Weather Rating	Type 3R

### Dimensions

Dimensions	2.44 in x 10.0 in x 12.0 in
Height	12.0 in
Length	2.44 in
Weight	7 lb
Width	10.0 in

### Electrical Ratings

Signal	Phone Line
--------	------------

### Certifications and Compliance

Certified Listed	UL/IC/FCC
------------------	-----------

### Product Assets

[Brochures - Rugged Telephone Brochure](#)  
[Installation Manuals - Telephone Management Application Installation Bulletin](#)  
[Installation Manuals - SMART Auto-Dial Handset Telephones Model 227-005, 247-005, 257-005, and 277-005](#)  
[Installation Manuals - Telephone Management Application \(TMA\) User Guide](#)  
[Literature - SMART Rugged Telephones - Auto-dial](#)  
[Literature - Telephone Management Application \(TMA\)](#)