




APEX CXe

Increased Safety and Dust Protection
Certified ATEX / IECEx / UKEX



Features

- Robust Inspectable Clamping arrangement for braid and tape
- Avoids any coldflow effects on the inner sheath of the cable
- DTS01 as standard

The Apex CXe Cable Gland is certified Exe, robust and for use with unarmoured, wire braid 'X', steel tape armour 'Z', elastomer and plastic insulated cables. The gland provides an IP and retention seal onto the cable outer sheath. This cable gland can be utilised to avoid the effects of coldflow on the inner sheath of the cable.

Cable Gland Selection Table

Cable Gland Selection Table										
Trade Size	Entry Thread Size 'A'			Cable Acceptance Details				Max Length 'E'	Hexagon Dimensions	
	Metric	NPT	Inner Sheath 'B'	Outer Sheath 'C'		Armour / Braid Thickness 'D'				
						X Ring				
			Max.	Min.	Max.	Orientation 1	Orientation 2		Across Flats	Across Corners
O	M16 M20	1/2"	12.0	7.2	16.0	0 - 0.8	-	52.5	24.0	26.5
A	M20	1/2" 3/4"	14.3	12.5	20.8	0 - 0.8	-	55.0	30.0	32.5
B	M25	3/4" 1"	20.2	18.0	27.0	0 - 0.7	0.5 - 1.0	60.5	36.0	39.5
C	M32	1" 1 1/4"	26.5	24.5	33.0	0 - 0.7	0.5 - 1..25	63.5	46.0	50.5
C2	M40	1 1/4" 1 1/2"	32.5	31.0	41.5	0 - 0.7	0.5 - 1..25	69.5	55.0	60.6
D	M50	1 1/2" 2"	42.3* 44.5	36.0	51.7	0 - 0.7	0.5 - 1.6	88.0	65.0	70.8
E	M63	2" 2 1/2"	54.3* 56.3	53.0	64.5	0 - 0.7	0.5 - 1.6	86.0	80.0	88.0
F	M75	2 1/2" 3"	65.3* 68.3	64.0	77.5	0 - 0.7	0.5 - 1.6	87.5	95.0	104.0

Os - F size metric entry threads are 1.5mm pitch as standard, 15mm length of thread
Alternative thread lengths may be available upon request.

*Smaller diameters apply when selecting smaller diameter NPT entry threadform.

Ordering Information

If brass is required please omit material selection
Format for ordering is as follows:

Cable Gland Type	Size	Thread	Material
CXe	C	M32	NP
CXe	C	1.0	NE

Order Example: CXeCM32NP

Please note all NPT entries should be state as a decimal

Please refer to part code logic information page for further details on product options

Technical Data	
Metallic Material Options	Manufactured in Brass, Nickel Plated Brass or 316L Stainless Steel. Metallics conform to EN10204 2.2 & 3.1
Non Metallic Materials	Thermoset Elastomer
Ingress Protection	IP66, IP67
Enclosure Protection	IK08 to IEC 62262
Deluge Protection	to DTS01
Operating Temperature	-60°C to +130°C
Applications	Suitable for use in Gas Zones 1,2 and Dust Zones 20, 21,22
Approvals	
Protection Class	Ex II 2G Ex eb IIC Gb; 3G Ex nR IIC Gc; 1D Ex ta IIIC Da
ATEX Certificate No	CML23ATEX1002X CML19ATEX4507X (Ex nR)
IECEX Certificate No	CML23.0001X CML21.0012X (Ex nR)
UKEX Certificate No	CML23UKEX1004X CML21UKEX4133X (Ex nR)
Construction & Test Standards	IEC/EN 62444 (Anchorage Type A), IEC/EN 60079-0, 7, 15, 31
Marine Approvals	ABS: 23-2419600. BV: 43523
Additional Certifications	Inmetro: IEx23.0108X. EAC: EA9C KZ 7100841.01.01.03125. PESO: P563425



A Hubbell brand