

RED ALERT® VoIP Hands-free Emergency Telephones - Model 393-710

By GAI-Tronics
Catalog # 393-710



GAI-TRONICS' RED ALERT® Hands-free VoIP Surface-mount Telephones are designed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

General

Application	Emergency Telephone Communications (campuses, parking lots, paths)
Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	Emergency Telephones HELP Button
Weather Rating	Type 3R

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Height	9.5 in
Length	4 in
Weight	4 lb
Width	8 in

Electrical Ratings

Signal	Ethernet
Voltage Rating Description	24-48 VDC or PoE

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Installation Manuals - RED ALERT® Hands-free VoIP Telephone Manual](#)
- [Literature - VoIP Hands-free Telephones - Surface-mount](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
GTC-393710-SPEC-EN | REV 6/2024