




150/RAC

Industrial gland for indoor use

International Approvals



Features

- Reversible Armour Clamp - For all types of armour and braid

The 150/RAC Cable Gland is an industrial gland for indoor or outdoor use, robust and for use with single wire armour, wire braid, steel tape armour, elastomer and plastic insulated cables.

Cable Gland Selection Table

Size Ref.	Entry Thread		Cable Acceptance Details				'G'	Hexagon	
	Metric	NPT* Standard	Inner Sheath	Outer Sheath 'B'	Armour Braid 'C'			Across Flats	Across Corners
			Max.	Max.	Orientation 1	Orientation 2			
O	M20 ²	½"	11.9	16.0	0.8 / 1.25	0.0 / 0.8	37.0	24.0	26.5
A	M20	¾" or ½"	14.3	20.5	0.8 / 1.25	0.0 / 0.8	38.2	30.0	32.5
B	M25	1" or ¾"	20.2	26.0	1.25 / 1.6	0.0 / 0.7	42.7	36.0	39.5
C	M32	1¼" or 1"	26.5	33.0	1.6 / 2.0	0.0 / 0.7	46.9	46.0	50.5
C2	M40	1½" or 1¼"	32.5	41.0	1.6 / 2.0	0.0 / 0.7	49.9	55.0	60.6
D	M50	2" or 1½"	44.4 / 42.3 ¹	52.6	1.8 / 1.25	0.0 / 1.0	63.5	65.0	70.8
E	M63	2½" or 2"	56.3 / 54.3 ¹	65.3	1.8 / 2.5	0.0 / 1.0	60.4	80.0	88.0
F	M75	3" or 2½"	68.2 / 65.3 ¹	78.0	1.8 / 2.5	0.0 / 1.0	63.2	95.0	104.0

All dimensions in millimetres (except * where dimensions are in inches). O - F size metric entry threads are 1.5mm pitch as standard, 15mm length of thread.

1 Smaller value is applicable when selecting reduced NPT entry option.

2 Sizes Os and O are available with an M16 thread size. For O size with M16 thread, the maximum cable inner sheath diameter is 10.9mm

Technical Data

Material Options	Manufactured in Brass, Nickel Plated Brass or 316L Stainless Steel
Construction & Test Standards	BS EN 62444:2013 (Anchorage Type D), BS 6121: Part 1 Type BW, TX, BY and BZ
Enclosure Protection	IK10 to IEC 62262
Operating Temperature	-60°C to +100°C

Ordering Information

If brass is required please omit material selection

Format for ordering is as follows: Alternative Ring (R), add suffix R to ordering information

Cable Gland Type	Size	Thread	Material	(Optional)
150	C	M32		R
150	C	1.25	NP	R

Order Example: 150CM32R

Alternative Reversible Armour Clamping Ring Size Selection

Size Ref	Orientation 1	Orientation 2
B	0.9 - 1.25	0.5 - 0.9
C	1.2 - 1.6	0.6 - 1.2
C2	1.2 - 1.6	0.6 - 1.2
D	1.45 - 1.8	1.0 - 1.45
E	1.45 - 1.8	1.0 - 1.45
F	1.45 - 1.8	1.0 - 1.45



A Hubbell brand