

RED ALERT® VoIP Hands-free Emergency Telephones - Model 394AL-712

By GAI-Tronics
Catalog # [394AL-712](#)



GAI-TRONICS' RED ALERT® Hands-free VoIP Surface-Mount Telephones are designed to provide direct point-to-point communication between personnel throughout a facility over an existing Internet Protocol LAN. The VoIP telephones are intended for connection to a 10/100 BaseT Ethernet and operate using power-over-Ethernet or an alternative power source. The VoIP telephone features real-time alarm reporting that enables system supervisors to monitor the phone's activity and address callers needs or maintenance issues immediately.

Features

- Power Over Ethernet or Alternative 24-48 V dc Supply
- SIP Compatible
- Four Inputs and Two Outputs Per Phone
- Auto Answer
- Multicast Capable (Up to 8 Addresses)

Application

Emerg. Telephone Comm., wireless (campuses, parking lots, paths)

General

Catalog Number	394AL-712
Color	Yellow
Connectivity Options	VoIP
Mount location	Surface-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55°C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Specifications	UL/CSA, FCC
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	<ul style="list-style-type: none"> • Emergency Telephones • HELP Button
Weather Rating	Type 3R

Dimensions

Dimensions	4.0 in x 8.0 in x 9.5 in
Dimensions - Shipping	13.0 x 12.0 x 8.0
Height	9.5 in
Length	4 in
Weight	7.8 lb
Width	8 in

Electrical Ratings

Signal	WiFi
Voltage Rating Description	24-48 VDC

Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

Product Assets

[Brochures - Red Alert Telephone Brochure](#)
[Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
[Configuration Guide - VoIP Telephone Configuration Guide:](#)
[Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
[Literature - VoIP Hands-free Telephones - Surface-mount](#)
[Specifications - 394AL712](#)
[Video - Gai-Tronics Emergency Phones](#)