

# RED ALERT® WiFi VoIP Flush-mount Telephones - Model 398-811A

By GAI-Tronics  
Catalog # 398-811A

These WiFi VoIP Flush-Mount Telephones are designed to provide direct point-to-point communications between personnel over an existing wireless local area network (WLAN), meeting IEEE 802.11 b/g standards. These telephones will operate from an external dc power source which is the only wiring required for operation.



## General

Application	Emerg. Telephone Comm., wireless (campuses, parking lots, paths)
Color	Silver
Connectivity Options	WiFi VoIP
Construction	Front Panel: 14-Gauge Type 304 Brushed Stainless Steel; Dust Cover: 16-Gauge Cold-Rolled Steel With Black Polyurethane Finish
Mount location	Flush-Mount
Operating Temperature	-4°F to +131°F / -20°C to +55 °C
Output Level Speaker	87 dB @ 1 M
Signal Type	VoIP - SIP
Storage Temperature Range	-40° C to +70° C
Temperature Rating	-4°F to +131°F (-20°C to +55°C)
Type	CALL Button  Keypad
Weather Rating	Type 3R

## Dimensions

Dimensions	2.38 in x 10.0 in x 12.0 in
Height	12 in
Length	2.38 in
Weight	7.2 lb
Width	10 in

## Electrical Ratings

Signal	WiFi
Voltage Rating Description	24-48 VDC

## Certifications And Compliance

Certification	UL/CSA/FCC
Certified Listed	UL/CSA/FCC
Compliance	FCC CRF 47 Part 15

## Product Assets

- [Brochures - Red Alert Telephone Brochure](#)
- [Configuration Guide - VoIP Telephone Configuration Guide: Firmware versions 1193 Telephones \(v1.08\); 1201 Telephones for Auteldac 6 \(v1.08\)](#)
- [Configuration Guide - VoIP Telephone Basic Configuration Guide](#)
- [Installation Manuals - RED ALERT® Hands-free WiFi VoIP Telephone Manual](#)
- [Literature - WiFi VoIP Hands-free Telephones - Flush-mount](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
GTC-398811A-SPEC-EN | REV 6/2024