

Plant Paging/Intercom Station

By GAI-Tronics
Catalog # [730-207](#)

Outdoor Wall Station, Single-Party Line, NRTL Listed for USA and Canada Class I, Div. 2, Groups A, B, C, D consists of: Amplifier (Model 701-307) and Enclosure (Model 733-002)



General

Color	Gray
Material	Steel / GRP
Output Level Speaker	8 / 16 Ohm
Power	12 W
Series	Page/Party®
Signal Type	Analog
Weather Rating	Outdoor

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5
Height	14.6 in
Weight	16.4 lb
Width	10.9 in

Electrical Ratings

Signal	33 Ohm
--------	--------

Certifications and Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Brochures - Page/Party® Solutions Brochure](#)
[Brochures - Page/Party® Accessories Guide](#)
[Installation Manuals - 700 Series 24 VDC Page/Party® System Design and Installation](#)

Related Products

[701-307 - Plant Paging/Intercom Amplifier](#)
[733-002 - 733-002, Weatherproof Non-Metallic Enclosure with 24 VDC operation](#)