

## Ex Sounder (230 VAC)

By GAI-Tronics  
 Catalog # [BEXS110D230AC](#)

This range of light weight all GRP, flameproof sounders intended for use in potentially explosive atmospheres has been designed with high ingress protection to cope with the harsh environmental conditions found offshore and onshore in the oil, gas and petrochemical industries. The flameproof alarm sounders are suitable for Zone 1 & Zone 2 applications.



### Features

- Zone 1 and Zone 2 use
- Ratchet adjustable stainless steel 'U' bracket
- 230 V ac
- Marine grade copper free LM6 Aluminium
- Phosphated & powder coated finish-anti-corrosion
- Automatic synchronisation on multi- sounder system
- 32 Tones comply with UKOOA/PFEER guidelines
- IP66 and IP67
- RAL3000 Red colour
- Dual M20 ISO cable entry
- 0.5 to 4.00mm<sup>2</sup> cables
- 3 remotely selectable stages

### General

Ingress Protection	IP66 and IP67
Material	Marine grade copper free LM6 Aluminium and ratchet adjustable stainless steel 'U' bracket
Operating Temperature	-50° C to +70° C

### Dimensions

Weight	7.05479 lb
--------	------------

### Certifications And Compliance

Certification	ATEX Cert.: KEMA 99ATEX6312 IECEX Cert.: IECEX KEM 10.0003 Inmetro Cert.: 10-IEEx-0009 GOST-R Cert.: POCC GB.ГБ05.В03365
Hazardous Rating(s)	Zone 1 Zone 2

### Product Assets

[Literature - EX Sounder](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
GTC-BEXS110D230AC-SPEC-EN | REV 6/2024