

# HUBBCOM™ IP Device with Temperature Sensing (Flush-mount, Handset)

By GAI-Tronics  
Catalog # [GSC3100TS](#)

The HUBBCOM™ IP device has a multi-functional design, providing solutions for all your control and communication needs. It provides the ability to combine web application control, VoIP SIP telephone operation, speaker broadcasts, and point-to-point serverless IP communication (audio and/or video). HUBBCOM™ TS devices add another critical function for security applications. This model adds a temperature sensor to the access control feature. After scanning their card, the user simply aligns themselves with the template on the screen and the station will read their temperature. Access will be granted if their temperature is within a programmable range.

## Features

- Card Access control with built-in pre-entry temperature check
- Point-to-Point, Serverless Audio & Video
- Paging with Intercom (Soft Zoning, Multiple Conference Calls, Serverless)
- SIP Telephone
- Web Portal Access (applications)
- 7-inch Capacitive Touchscreen
- ONVIF-Compatible HD Camera
- Flush-mount / Handset
- Intuitive Operation
- 24 V dc or PoE / PoE+ Input
- Integral 2 W Speaker
- 8 Ohm, 8 W Speaker Output
- Two (2) Isolated Volt-free Outputs
- WiFi (802.11 a/b/g/n + MIMO)
- Bluetooth (Version 4.1 + CSA2 support / BLE)

## General

Connectivity Options	VoIP
Operating Temperature	0° C to 50° C
Power	PoE / PoE+, 802.3af compliant (via RJ45)
UPC	850025795418



## Dimensions

Weight 5 lb

## Certifications and Compliance

Compliance FCC CRF 47 Part 15

## Product Assets

[Brochures - HUBBCOM™ Solutions Brochure - Communications & Control](#)  
[Brochures - HUBBCOM™ Solutions Brochure - Communications & Control \(spread\)](#)  
[Catalogs - Transportation - Rail Industry](#)  
[Installation Manuals - ADDENDUM-HUBBCOM™ Temperature Sensor Configuration and Operation](#)  
[Installation Manuals - HUBBCOM™ Dual-Port Flush-Mount Smart Controllers](#)  
[Literature - HUBBCOM™ IP Devices with Temperature Sensing](#)

## Related Products

[Surface-Mount Enclosure - 238 Series](#)  
[238-001 - Surface-Mount Enclosure - 238 Series](#)