

# Indoor/Outdoor Compression Driver - 13314 Series (8 ohm)

By GAI-Tronics  
Catalog # [13314-001](#)

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.



## Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

## General

Operating Temperature	-40° C to +70° C (-40° F to +158° F)
UPC	850025795142

## Dimensions

Weight	3.1 lb
--------	--------

## Electrical Ratings

Impedance	8 ohm
-----------	-------

## Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Div. 2, Groups A, B, C, D</li><li>• Class II, Div. 2, Groups F, G</li><li>• Class III, Div. 2</li></ul>
Nema Rating	4X

## Product Assets

- [Installation Manuals - Model 13314-001 Div. 2 Hazardous Area 8-Ohm Horn Driver](#)
- [Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)
- [Literature - Indoor / Outdoor Compression Driver](#)

## Related Products

- [13305-101 - Bi-Directional Horn - Model 13305-101](#)
- [13304-002 - Aluminum Horns - Model 13304-002](#)
- [13306-101 - Aluminum Horn - Model 13306-101](#)
- [13302-002 - Aluminum Horns - Model 13302-002](#)
- [13340 - Constant Directivity Horn - Model 13340](#)