PTC Series

Cable ID & Phase Tracing System

■ The PTC Series Phase Tracing System is ideal for identifying individual phases of three-phase direct buried or conduit installed cable. The PTC Series is designed to positively identify cable phases at a point where many cables come together. Such as cable used in power circuits, feeders and distribution networks. This device will also identify each individual phase in three-phase power cable.

PRECI

This Phase Tracing System has three major components: a pulse transmitter, pulse detector and pick up coil. It's recommended that the cable is disconnected from any load impedance and the threephase conductors are tied together and grounded at the far end. However, this device will operate in a satisfactorily manner while connected to low impedance loads.



FEATURES

Transmitter

- Continuously adjustable output current
- ☑ Low operating voltage
- ☑ Output current meter
- ☑ Input circuit breaker switch with ON pilot light

Detector

- High gain transistor amplifier circuit
- ☑ Sensitive pickup coil
- ☑ Rotary switch with OFF and five sensitivity levels
- ☑ 50 division meter to indicate relative strength of signal

BENEFITS

Effective phase identification on shielded, unshielded and lead-jacketed cable.

Complete, compact and portable system for simple and quick use in the field.

Minimal setup time and simple control panel.

APPLICATIONS

- Electrical Utilities
- Test Companies
- Petrochemical Facilities
- Facility Maintenance



TECHNICAL SPECIFICATIONS

PRECIS

Model Number		PTC2-*		
System Output		0-30V @ 30A		
Pulse	Shape	Square Wave (Fig. 2)		
	Width	830 msec		
Repetition Rate	Continuous	1, 2 or 3 pulses per 5 sec in A, B & C Phases (Fig. 1)		
	Intermittent	A-Phase	12 pulses per 1 min & 2 pulses per 5 sec (Fig. 2)	
		B-Phase	24 pulses per 1 min & 2 pulses per 5 sec (Fig. 2)	
		C-Phase	Reciprocal of A and B in return leg (Fig. 2)	
Dimensions (W x H x D)	Transmitter	12 x 7.5 x 12.25 in (30.5 x 19.1 x 31.1 cm)		
	Detector	6.75 x 6 x 3.5 in (17.1 x 15.2 x 8.9 cm)		
	Pick-Up Coil	2.5 x 2.75 x 2.5 in (6.4 x 7 x 6.4 cm)		
Weight	Transmitter	Net	41 lbs (18.6 kg)	
		Shipping	52 lbs (23.6 kg)	
	Detector	Net	4 lbs (1.82 kg)	
		Shipping	8 lbs (3.6 kg)	
	Pick-Up Coil	Net	1.75 lbs (.8 kg)	
		Shipping	4 lbs (1.8 kg)	
Input Voltage & Frequency		* In the model number, designate 'A' for 120V/60Hz input or 'B' for 220V/50Hz input		

SYSTEM DIAGRAM




Fig.2: Repetition Rate per Phase

OPTIONAL EQUIPMENT & ACCESSORIES

Part Number	Description	Input Voltage & Frequency	
8030TC-*	Extra Transmitter (30V, 3A) & Test Lead	* In the model number, designate 'A' for	
8012TC-*	Extra Transmitter (12V, 30A) & Test Lead	120V/60Hz input or 'B' for 220V/50Hz input	
TCD2A	Extra Detector	N/A	
8030-LS	Extra Test Leads		
EXT-WARN-1 One year extended warranty			

OFFICES:

Europe Haefely Test AG Birsstrasse 300 4052 Basel Switzerland

 China Haefely Test AG Representative Beijing Office 8-1-602, Fortune Street No. 67, Chaoyang Road, Chaoyang District Beijing, China 100025

North America Hipotronics, Inc.

1650 Route 22 N Brewster, NY 10509 United States

HAEFELY HIPOTRONICS has a policy of continuous product improvement. We therefore reserve the right to thange design and specification without notice.