


Cable Glands Hazardous Area

Increased Safety, Dust Protection
Class - Zones - Divisions
Certified ATEX / IECEx / c CSA us

Application

The 321/R cable gland provides a seal and cable clamp on the outer cable sheath and is intended for use on non-armoured elastomer and plastic insulated cables. The cable gland certified Exe and is suitable for installation in Zone 1 (21) and Zone 2 (22) hazardous areas.



CABLE GLAND SELECTION TABLE

Size Ref.	Entry Thread Size		Cable Acceptance Details				'G'	Hexagon Dimensions	
	Metric	NPT * Standard or Option	Outer Sheath 'B'					Across Flats	Across Corners
			Standard Seal		Alternative Seal (S)				
			Min.	Max.	Min.	Max.			
Os	M20 ¹	½"	3.2	8.0	-	-	52.0	24.0	26.5
O	M20 ¹	½"	6.5	11.9	-	-	52.0	24.0	26.5
A	M20	¾" or ½"	10.0	14.3	9.0	13.4	52.0	30.0	32.5
B	M25	1" or ¾"	13.0	20.2	9.5	15.4	54.0	36.0	39.5
C	M32	1¼" or 1"	19.5	26.5	15.5	21.2	61.0	46.0	50.5
C2	M40	1½" or 1¼"	25.0	32.5	22.0	28.0	67.0	55.0	60.6

¹T — Os - C2 size metric entry threads are 1.5mm pitch as standard, 15mm length of thread.
All dimensions in millimetres (except * where dimensions are in inches).

¹Sizes Os and O are available with an M16 thread size. For O size with M16 thread, the maximum cable outer sheath diameter is 10.9mm

Technical Data

ATEX/IECEx

- Increased Safety Exe IIC Gb and Dust Extb IIIC Db Ⓜ II 2 GD.
- Certificate No's: Baseefa06ATEX0059X and IECEx BAS 06.0016X.
- Suitable for use in Zone 1, Zone 2, Zone 21, Zone 22.
- Construction and Test Standards: IEC/EN 60079-0, IEC/EN 60079-7 and IEC/EN 60079-31.
- Ingress Protection: IP66, IP67 and IP 68 (30 metres for 7 days) to IEC/EN 60529 and NEMA 4X.
- Deluge Protection to DTS01.
- Operating Temperature Range: -60°C to +100°C.
- Assembly Instruction Sheet: AI 452.

cCSAus

- Increased Safety AExe IIC and Dust AExtD Zone 21.
- Explosion-proof Class 1 Division 2, Class II Division 2 Groups EFG, Class III.
- Certificate No's: CSA1205533 for Marine Shipboard Cable.
- Construction and Test Standards: UL 60079-0, UL 60079-7, ISA 60079-31.
- CSA 22.2 No: 60079-0, CSA 22.2 No: 60079-7, CSA 22.2 No: 60079-31, UL 2225

Features

- When used in Increased Safety applications, this cable gland may be used with braided cable where the braid and the outer sheath pass into the enclosure. The braid must then be suitably terminated inside the enclosure.
Note: Braided cable is classed as unarmoured cable in the EN/IEC 60079 series standards for Exe applications.
- Manufactured in Brass (standard), Nickel Plated Brass or 316 Stainless Steel.
- Brass NPT entries are nickel plated as standard.
- Cable clamp provides required clamp and cleat function

Ordering Information

Format for ordering is as follows:

Certification required i.e. ATEX / IECEx

Material & Finish i.e. Brass Nickel Plated

Alternative Seal (S), add suffix S to ordering information.

Cable Gland Type	Size	Thread	(Optional)
321/R	C	M32	S
321/R	C	1 ¼"NPT	S