


GRP ENCLOSURE

Increased Safety & Dust Protection





Maximum Quantity of Entries Per Face					
Thread Size	M16	M20			
Face C	2	2			
Face B & D	1	1			

Optional: Earth continuity plate.

Untapped clearance holes - threaded holes are not available due to wall thickness.

Terminal Capacity								
Terminal Type	Conductor size (mm²)		Max. Volts	Maximum Physical Terminal Content				
	Min.	Max.	IVIAA. VOICS	Terminal Quantity	An	nps		
WDU 2.5N	0.5	2.5	420	10	10			
UT 2.5	0.5	2.5	690	9	11			
WDU 2.5	0.5	2.5	550	9	10			
UT 4	0.5	4	690	8	12			
WDU 4	0.5	4	690	8	13			
UT 6	0.5	6	690	6	18			
HPB 4	0.5	Max. per Pillar	550	1	Conductor Size mm ²	Max. Amps per Pillar		
	See certificate	2 x 10mm ² 3 x 6mm ² 4 x 4mm ² 4 x 0.5mm ² 2 x 2.5mm ² solid 1 x 6.0mm ² stranded			0.5 0.75 1 1.5 2.5 4 6	1 1 8 10 15 21 26 37		

An earth terminal equal to that of the largest power terminal will be fitted.

For Junction Box Wattage Factor and Combined Terminal Resistance. See catalogue page TBA. Above max amps based on T6 +40°C.

The terminals listed are restricted to a minimum operating temperature of -50°C.

Max number of terminals may reduce the number of holes allowed.

CONNECTION SOLUTIONS For Global Applications

HUBBELL

Harsh & Hazardous

Product design and specifications are subject to change without notice, Please check the Hawke website for latest specifications. www.ehawke.com

Technical Data							
Type of Protection	Increased Safety 🖾 II 2 GD Exe IIC Gb, Extb IIIC Db	Ingress Protection	IP66 to EN60529				
Area Classification	Suitable for use in Zone 1, Zone 2, Zone 21, Zone 22	Material	Glass reinforced plastic (GRP) Natural Black Finish				
Certificates PL511 Certificate No's: Baseefa14ATEX0268X IECEX BAS 14.0123X		Operating Temperature	Range: -60°C to +75°C				
	ZPL511 Certificate No's: Baseefa14ATEX0248U IECEx BAS 14.0120U	T Class and Ambient	T6 40°C with optional T5 with ambients up to 65°C				
Construction and Test Standards	IEC/EN 60079-0, IEC/EN 60079-7 and IEC/EN 60079-31	Assembly Instructions	PL511: AI 260 ZPL511: AI 261				