


Enclosure Type: Size 1 (S1) Stainless Steel

S Series Enclosures

Increased Safety Exe Dual Certified ATEX / IECEx



Serrated Washers / Locknuts with large outside diameters may foul on adjacent glands.

* Serrated Washers / Locknuts must not foul on aperture wall.

Technical Data

- Increased Safety Ⓢ II 2 GD Exe II ExtD.
- Size 1 (S1) Certificate No's: Baseefa08ATEX0208X and IECEx BAS 08.0065X.
- Z Size 1 (ZS1) Certificate No's: Baseefa08ATEX0207U and IECEx BAS 08.0064U.
- Suitable for use in Zone 1, Zone 2, Zone 21 and Zone 22.
- Construction and Test Standards: IEC/EN 60079-0, IEC/EN 60079-7, IEC/EN 61241-0 and IEC/EN 61241-1.
- Ingress Protection: IP66 to IEC/EN 60529.
- Deluge Protection to DTS01.
- Operating Temperature Range: -60°C to +80°C.
- Temperature Class and Ambient: T6 40°C, optional T5 with ambients up to 65°C.
- Size 1 (S1) Assembly Instruction Sheet: AI 266.
- Z Size 1 (ZS1) Assembly Instruction Sheet: AI 267.
- 210mm deep option available.
- Alternative certification options available:



Exe II



AExe II / Exe II



GOST R-Exe IIU



GOST K- Approved for use in Kazakhstan

For full technical specification, see Page 32

TERMINAL CAPACITY

Terminal Type	Conductor Size (mm ²)		Max. Volts	Max. Physical Terminal Content		Reduced Terminal Content at Max. Terminal Amps	
	Min.	Max.		Terminal Qty.	Amps	Terminal Qty.	Amps
WDU 2.5	0.5	2.5	550	30	13	18	17
WDU 4	0.5	4	690	25	17	16	22
WDU 6	0.5	6	550	19	24	13	29
WDU 10	1.5	10	550	15	34	11	40
WDU 16	1.5	16	690	13	45	9	53
WDU 35	2.5	35	690	9	75	6	87

Notes: For Junction Box Wattage Factor and Combined Terminal Resistance, see Pages 43 & 44

The box is supplied with an integral internal / external earth stud assembly.

The terminals listed are restricted to a minimum operating temperature of -50°C.