



# 15 Kv Class Elbow Arrester (2.55 kV MCOV)

By Hubbell  
Catalog # [215ELA03](#)

Deadfront Elbow Arrester, 15kV 2.55 MCOV



\*Representative Image

## Features

- To learn more about identifying the right Elbow Arrester on varying applications, visit our blog [here](#).

## General

EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360537

## Dimensions

Height	6.600 in
Maximum Operating Altitude	6000 ft
Weight	3.700 lb

## Electrical Ratings

Duty Cycle	3 kV
MCOV	2.55 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"><li>9.8 kV @ 1.5 kA</li><li>10.3 kV @ 3 kA</li><li>11 kV @ 5 kA</li><li>12.3 kV @ 10 kA</li><li>14.3 kV @ 20 kA</li><li>18.5 kV @ 40 kA</li></ul>
Maximum Switching Surge Protective Level @ 500A	8.5 kV
kV Class	15 kV

## Logistics

Pallet Quantity	176
Standard Package	1

## Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Catalogs - Underground Arresters \(C6\)](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions \(IS-200ELA\)](#)
- [ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
- [Sales Drawings - 15 kV, 200A Loadbreak Elbow Arrester \(215ELA\)](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)
- [Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
HUBB-215ELA03-SPEC-EN | REV 9/2023