

The 153/RAC Cable Gland is an industrial gland for indoor or outdoor use, robust and for use with single wire armour 'W', wire braid 'X', steel tape armour 'Z', elastomer and plastic insulated cables. The gland provides an elastomeric seal on the cable inner sheath, and a low smoke, zero halogen IP and retention seal onto the cable outer sheath.

Cable G	Gland Se	lection	Table
---------	----------	---------	-------

	Entry Th	read Size 'A' Cable Acceptance Details								Hexagon Dimensions			
Size Ref.	Metric	NPT* Standard	Inner Sheath			Outer Sheath 'B'		Armour/Braid 'C'		'G'	Across	Across	
			5	itd Seal	Alt Se	eal (S)	Min	Max	Orientation 1	Orientation 2		Thats	Conners
Os	M20 ²	1/2″	3.2	8	-	-	5.5	12.0	0.8/1.25	0.0/0.8	52.0	24.0	26.5
0	M20 ²	1/2″	6.5	11.9	-	-	9.5	16.0	0.8/1.25	0.0/0.8	52.0	24.0	26.5
А	M20	3⁄4" or 1⁄2"	10	14.3	9	14.3	12.5	20.5	0.8/1.25	0.0/0.8	53.0	30.0	32.5
В	M25	1" or 3⁄4"	13	20.2	9.5	15.4	16.9	26.0	1.25/1.6	0.0/0.7	69.5	36.0	39.5
С	M32	1¼" or 1"	19.5	26.5	15.5	21.2	22.0	33.0	1.6/2.0	0.0/0.7	64.0	46.0	50.5
C2	M40	11/2" or 11/4"	25	32.5	22	28	28.0	41.0	1.6/2.0	0.0/0.7	68.3	55.0	60.6
D	M50	2" or 11/2"	31.5	44.4/42.3 ¹	27.5	34.8	36.0	52.6	1.8/2.5	0.0/1.0	79.0	65.0	70.8
E	M63	21/2" or 2"	42.5	56.3/54.3 ¹	39	46.5	46.0	65.3	1.8/2.5	0.0/1.0	78.9	80.0	88.0
F	M75	3" or 2½"	54.5	68.2/65.3 ¹	49.5	58.3	57.0	78.0	1.8/2.5	0.0/1.0	83.7	95.0	104.0
G	M80	31⁄2″	67	73	-	-	75.0	89.5	2.0/3.5	0.0/1.0	95.6	106.4	115.0
Н	M90	31⁄2″	67	77.6	-	-	75.0	89.5	2.0/3.5	0.0/1.0	95.6	115.0	130.0
J	M100	4″	77	91.6	-	-	88.0	104.5	2.5/4.0	0.0/1.0	95.6	127.0	142.0

All dimensions in millimetres (except * where dimensions are in inches).

Os - F size metric entry threads are 1.5mm pitch as standard, 15mm length of thread.

G - J size metric entry threads are 2mm pitch as standard, 20mm length of thread

¹Smaller value is applicable when selecting reduced NPT entry option.
²Sizes Os and O are available with an M16 thread size. For O size with M16 thread, the maximum cable outer sheath diameter is 10.9mm

Technical Data				
Material Options	Manufactured in Brass, Nickel Plated Brass or 316L Stainless Steel			
Construction & Test Standards	IEC/EN 62444 (Anchorage Type D)			
Ingress Protection	IP66, IP67 to IEC/EN 60529 and NEMA 4X			
	IK10 to IEC 62262			
Deluge Protection	DTS01			
Operating Temperature	-60°C to +100°C			

Ordering Information

If brass is required please omit material selection

Format for ordering is as follows: Alternative Seal (S), Alternative Ring (R), add suffix S and/or R to ordering information

=		-	-	
Cable Gland Type	Size	Thread	Material	(Optional)
153R	С	M32		R
153R	С	1.25	NP	S

Order Example: 153RCM32R

Please note all NPT entries should be state as a decimal

Please refer to part code logic information page for further details on product options





Alternative Reversible Armour Clamping Ring Size Selection					
Size Ref	Orientation 1	Orientation 2			
В	0.9 - 1.25	0.5 - 0.9			
С	1.2 - 1.6	0.6 - 1.2			
C2	1.2 - 1.6	0.6 - 1.2			
D	1.45 - 1.8	1.0 - 1.45			
E	1.45 - 1.8	1.0 - 1.45			
F	1.45 - 1.8	1.0 - 1.45			

Cable Gland Tightening Guide

Whilst Hawke International goes to great lengths to ensure products are designed to be as simple to install, inspect and maintain as is possible, differing levels of competency, training and understanding can lead to glands being incorrectly installed. With hazardous area products, any poor installation issues can not only lead to expensive equipment failure, but also potential explosion risks and associated risk to life.

To help address issues with the overtightening of cable glands and the resultant damage to cables and seals, Hawke International has developed the patented **INBUILT TIGHTENING GUIDE**.

Without the need for fiddly measuring systems, the guide provides a permanent visual indication of the gland tightness through installation, inspection and maintenance.

How it works

The gland is permanently marked with various lines/numbers indicating the correct tightening level related to the cable diameter. Following the relevant cable gland Installation Instructions, the back seal should be tightened until a seal is formed on the cable outer sheath and then tightened one further turn.



Follow cable gland installation instructions until final stage – tightening of rear seal



Tighten backnut until a seal is formed onto the cable, then tighten one further turn



The backnut should be level with the marking guide corresponding to its diameter – this can be visually inspected and adjusted as necessary

Note: The cable gland installation instructions have a printed cable OD measure for if the cable OD is not known



