

15kV Load Break Feed-Thru, Horizontal

By Hubbell Power Systems
Catalog # 215FT



Load Break Feed-Thru, Horizontal, 200 Amp, 15 kV.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Position	Horizontal
Type	200Amp Load Break
UPC	096359392453

Dimensions

Dimensions	5.500 in x 7.500 in x 10.000 in
Height	10.000 in
Length	5.500 in
Weight	3.750 lb
Width	7.500 in

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Logistics

Pallet Quantity	200
Standard Package	1

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - IS-200FTI_Rev_A_Oct_2016](#)
[Installation Manuals - Loadbreak Connector Installation and Operating Instructions \(IS-200FT\)](#)
[Sales Drawings - Feed -Thru 15 kV \(215FT\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors \(G11-12-01\)](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)