

15 kV, Load Break Elbow w/ Bimetal Contact, Seal Kit

By Hubbell Power Systems
Catalog # 215LE33J

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact,
Cable Insulation Diameter range = 0.495 - 0.730 inches, #1
Solid or Compacted and #2 Stranded or Compressed



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Bi-Metal
Integral Seal	No
PROBELOK® Connectors	No
Type	200Amp Load Break
UPC	096359711780
With Seal Kit	Yes
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	0.730 in
Cable Insulation Diameter Minimum	0.495 in
Weight	3.250 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.495 - 0.730
Solid or Compacted Conductor	#1
Stranded or Compressed Conductor	#2

Logistics

Pallet Quantity	240
Standard Package	20

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors \(IS-200LUGB\)](#)
[Installation Manuals - 200A, 15kV & 25kV Class Elbows \(IS-200LE\)](#)
[Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors \(G11-12-01\)](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)