




# GMC

Gland Mounted Clamp For Hawke Cable Glands



The Hawke GMC is a retro fittable clamp intended for use where additional cable support is required.

## Features

Provides additional cable support and pullout resistance	Manufactured in 316 Stainless Steel
3-Part design allows clamp to be retrospectively fitted	Offers clamping solution in accordance with BS EN 60079-14 10.3
Captive fittings for easy installation	Suitable for all styles of Hawke cable gland listed below

## Clamp Selection Table For Cable Glands

Clamp Size	Type	Os	O	A	B	C*
Size 2						
Size 3						
Size 4						
Size 5						

\*Max cable diameter 27.5mm

## Suitable for Hawke Cable Glands


APEX Series,  
 501/421, 501/423, 501/453/RAC, 501/453/UNIV,  
 ICG653/UNIV, PSG553/RAC, 501/453/RAC/L,  
 ICG653/UNIV/L, 121, 123, 151/RAC, 153/RAC, 153/UNIV,  
 153/RAC/L, 653/UNIV, 453/RAC, 453/UNIV

## Ordering Example

Gland Mounted Clamp / Size 1

## Installation Steps

- 1 Unscrew tail nut and slide down the cable.
- 2 Choose correct mounting ring from two options supplied (a or b) and drop onto cable.
- 3 Slide mounting ring onto the gland and re-install the backnut. The clamp mounting ring should now be retained on the gland.
- 4 Hook the clamp arms onto the clamp mounting ring.
- 5 Rotate the clamp arms 90 degrees and pre-engage the screws. Do not yet tighten.
- 6 Whilst the clamp is still loose, pull it in the direction shown to ensure it is up against the backnut.
- 7 Tighten the screws. It is recommended to incrementally tighten each screw to ensure the clamp is tightened equally on both sides.



A Hubbell brand