

15 kV, Load Break Elbow w/ Test Point, Bimetal Contact

By Hubbell Power Systems
Catalog # [215LE44T](#)

Load Break Elbow, 200 Amp, 15 kV, with Test Point, Long Bimetal Contact, Cable Insulation Diameter range = 0.635 - 0.905 inches, 1/0 Solid or Compacted and #1 Stranded or Compressed



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Bi-Metal
EU RoHS Indicator	No
Integral Seal	No
PROBELOK® Connectors	No
Type	Load Break Elbows
UPC	096359509745
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	0.905 in
Cable Insulation Diameter Minimum	0.635 in
Dimensions	9.00 in x 9.00 in x 4.00 in
Height	4.00 in
Length	9.00 in
Weight	2.750 lb
Width	9.00 in

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.635 - 0.905
Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

Logistics

Carton Quantity	20
Pallet Quantity	240
Standard Package	20

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors \(IS-200LUGB\)](#)
[Installation Manuals - 200A, 15kV & 25kV Class Elbows \(IS-200LE\)](#)
[Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
[Sales Drawings - Elbow, 200A 15 kV \(215LE\)](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors \(G11-12-01\)](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)

