

15kV Load Break Elbow, 200 Amp, with Test Point, Size 5

By Hubbell Power Systems Catalog # 215LE50T

Load Break Elbow, 200 Amp, 15 kV, with Test Point.



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Integral Seal No PROBELOK ® Connectors No

Type Load Break Elbows UPC 096359506195

With Seal Kit No
With Test Point Yes

Dimensions

Cable Insulation Diameter 1.135 in

Maximum

Cable Insulation Diameter 0.760 in

Minimum

Dimensions 9.00 in x 9.00 in x 4.00 in

 Height
 4.00 in

 Length
 9.00 in

 Weight
 2.750 lb

 Width
 9.00 in

Electrical Ratings

AC Withstand Voltage (1 min) 34 kV
Basic Impulse Level 95 kV
Corona Extinction (3pC) 11 kV
Current Rating 200 A
kV Class 15 kV

Conductor Related

Cable Insulation Diameter 0.760 - 1.135

Range

Logistics

Pallet Quantity 240 Standard Package 20

Product Assets

Catalogs - Cable Accessories (C7)

Literature - Loadbreak Elbow Infographic (GR03087E)

Sales Drawings - Elbow, 200A 15 kV (215LE)

SDS - VERSILUBE G661 SILICONE COMPOUND

Test Documents - ANSI/IEEE Design Test Report - 15kV 200A

Loadbreak Separable Connectors (G11-12-01)

Video - 200A Loadbreak Elbow Fault Closure (VI03045E)

Video - Grease Best PRactices (HPS CA UTL VI EN 00030)