

15 kV, Load Break Elbow w/ Bimetal Contact, Shield Adapter Kit

By Hubbell Power Systems
Catalog # [215LE55S](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 0.760 - 1.135 inches, 2/0 Solid or Compacted and 1/0 Stranded or Compressed



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

| | |
|----------------------|-------------------|
| Connector Type | Bi-Metal |
| Integral Seal | No |
| PROBELOK® Connectors | No |
| Type | Load Break Elbows |
| With Seal Kit | Yes |
| With Test Point | No |

Dimensions

| | |
|-----------------------------------|----------|
| Cable Insulation Diameter Maximum | 1.135 in |
| Cable Insulation Diameter Minimum | 0.760 in |
| Weight | 3.250 lb |

Electrical Ratings

| | |
|-------------------------------|-------|
| AC Withstand Voltage (1 min) | 34 kV |
| Amperage Rating | 200 A |
| Basic Impulse Level | 95 kV |
| Corona Extinction (3pC) | 11 kV |
| Current Rating | 200 A |
| DC Withstand Voltage (15 min) | 53 kV |
| Voltage Rating | 15 kV |

Conductor Related

| | |
|----------------------------------|---------------|
| Cable Insulation Diameter Range | 0.760 - 1.135 |
| Solid or Compacted Conductor | 2/0 |
| Stranded or Compressed Conductor | 1/0 |

Logistics

| | |
|------------------|-----|
| Pallet Quantity | 120 |
| Standard Package | 20 |

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
[SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)
[Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
[Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)