

## 15 kV, Load Break Elbow w/ Bimetal Contact, Shield Adapter Kit

By Hubbell Power Systems  
Catalog # [215LE57S](#)

Load Break Elbow, 200 Amp, 15 kV, Long Bimetal Contact, Shield Adapter Kit, Cable Insulation Diameter range = 0.760 - 1.135 inches, 4/0 Solid or Compacted and 3/0 Stranded or Compressed



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Bi-Metal
Integral Seal	No
PROBELOK® Connectors	No
Type	Load Break Elbows
With Seal Kit	Yes
With Test Point	No

### Dimensions

Cable Insulation Diameter Maximum	1.135 in
Cable Insulation Diameter Minimum	0.760 in
Weight	3.250 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Amperage Rating	200 A
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
DC Withstand Voltage (15 min)	53 kV
Voltage Rating	15 kV

### Conductor Related

Cable Insulation Diameter Range	0.760 - 1.135
Solid or Compacted Conductor	4/0
Stranded or Compressed Conductor	3/0

### Logistics

Pallet Quantity	120
Standard Package	20

### Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
- [SDS - Safety Data Sheet - Versilube G661 Silicone Compound](#)
- [Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
- [Video - Grease Best Practices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)