

## 25kV Parkingstand Arrester (10.2 kV MCOV)

By Hubbell Power Systems  
Catalog # [225PLA12](#)

Deadfront Parkingstand Arrester.



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

### General

|                 |                       |
|-----------------|-----------------------|
| Bracket Type    | Parkingstand Bracket  |
| Grounding Style | 36 in Line Lead       |
| Material        | Polymer               |
| Type            | Underground Arresters |

### Dimensions

|                            |           |
|----------------------------|-----------|
| Height                     | 10.200 in |
| Maximum Operating Altitude | 6000 ft   |
| Weight                     | 4.600 lb  |

### Electrical Ratings

|   |  |
|---|--|
| Duty Cycle                                      | 12 kV  |
| MCOV  | 10.2 kV  |
| Maximum Discharge Voltage                       | <ul style="list-style-type: none"><li>• 39 kV @ 1.5 kA</li><li>• 41 kV @ 3 kA</li><li>• 44 kV @ 5 kA</li><li>• 49 kV @ 10 kA</li><li>• 57 kV @ 20 kA</li><li>• 74 kV @ 40 kA</li></ul> |
| Maximum Switching Surge Protective Level @ 500A | 34.0 kV  |
| kV Class  | 25 kV  |

### Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

### Product Assets

[Catalogs - Cable Accessories \(C7\)](#)  
[Catalogs - Underground Arresters \(C6\)](#)  
[Installation Manuals - Parkingstand Arrester Installation and Operating Instructions \(IS-200PLA\)](#)  
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)  
[Sales Drawings - 225PLAXX](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)  
[Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)