

25kV Parkingstand Arrester (12.7 kV MCOV)

By Hubbell Power Systems
Catalog # [225PLA15](#)

Deadfront Parkingstand Arrester.



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Bracket Type	Parkingstand Bracket
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359668978

Dimensions

Height	10.200 in
Maximum Operating Altitude	6000 ft
Weight	4.600 lb

Electrical Ratings

Duty Cycle	15 kV
MCOV	12.7 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 45.5 kV @ 1.5 kA• 48.5 kV @ 3 kA• 52 kV @ 5 kA• 57.5 kV @ 10 kA• 67.5 kV @ 20 kA• 87.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	40.0 kV
kV Class	25 kV

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Catalogs - Underground Arresters \(C6\)](#)
- [Installation Manuals - Parkingstand Arrester Installation and Operating Instructions \(IS-200PLA\)](#)
- [ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
- [Sales Drawings - 225PLAXX](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)
- [Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)