

25/28kV Fused Elbow, with cable insulation dia of 0.920 - 1.185 in, Hi-Tech® Fuse Connector

By Hubbell Power Systems
Catalog # [228FEHC8](#)

Fused Elbow, 25/28 kV, with Test Point, Cable Insulation Diameter range = 0.920 - 1.185 inches, 250 Compact and 4/0 Stranded or Compressed, Accepts Hi-Tech® EFX Current Limiting Fuses



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

| | |
|----------------------|-------------------------|
| Connector Type | Hi-Tech® Fuse Connector |
| Integral Seal | No |
| PROBELOK® Connectors | No |
| Type | 200A Loadbreak |
| With Seal Kit | No |
| With Test Point | Yes |

Dimensions

| | |
|-----------------------------------|----------|
| Cable Insulation Diameter Maximum | 1.185 in |
| Cable Insulation Diameter Minimum | 0.920 in |
| Weight | 7.5 lb |

Electrical Ratings

| | |
|------------------------------|----------|
| AC Withstand Voltage (1 min) | 45 kV |
| Basic Impulse Level | 125 kV |
| Corona Extinction (3pC) | 21.5 kV |
| Current Rating | 200 A |
| kV Class | 25/28 kV |

Conductor Related

| | |
|----------------------------------|---------------|
| Cable Insulation Diameter Range | 0.920 - 1.185 |
| Solid or Compacted Conductor | 250 |
| Stranded or Compressed Conductor | 4/0 |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - IS200FE_-_Fused_Elbow_Installation_Instructions](#)
[Sales Drawings - 228FE Sales Drawing](#)
[Test Documents - 28kV Fused Elbow Test Report](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)

