

## 25/28 kV, Load Break Elbow w/ Test Point, ProbeLok Bimetal Contact, Seal Kit

By Hubbell Power Systems  
Catalog # 228LE57PTJ

Load Break Elbow, 200 Amp, 25/28 kV, with Test Point, Long ProbeLok Bimetal Contact, Cable Insulation Diameter range = 0.920 - 1.310 inches, 4/0 Solid or Compacted and 3/0 Stranded or Compressed



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	ProbeLok Bi-Metal
Integral Seal	No
Type	Load Break Elbows
With Seal Kit	Yes
With Test Point	Yes

### Dimensions

Cable Insulation Diameter Maximum	1.310 in
Cable Insulation Diameter Minimum	0.920 in
Weight	3.500 lb

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

### Conductor Related

Cable Insulation Diameter Range	0.920 - 1.310
Solid or Compacted Conductor	4/0
Stranded or Compressed Conductor	3/0

### Logistics

Standard Package	20
------------------	----

### Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors \(IS-200LUGB\)](#)
- [Installation Manuals - 200A, 15kV & 25kV Class Elbows \(IS-200LE\)](#)
- [Literature - Loadbreak Elbow Infographic \(GR03087E\)](#)
- [Literature - ProbeLok® connectors](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors \(EU1552\)](#)
- [Test Documents - ProbeLock \(CH-9905\)](#)
- [Video - 200A Loadbreak Elbow Fault Closure \(VI03045E\)](#)
- [Video - Grease Best PRactices \(HPS\\_CA\\_UTL\\_VI\\_EN\\_00030\)](#)