

35 kV Class Large Interface Elbow Arrester (29 kV MCOV)

By Hubbell Power Systems
Catalog # [236ELA36](#)

ELBOW ARRESTER, 35KV 29 MCOV, Mates with IEEE Std. 386, Interface 9



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

| | |
|-------------------|-----------------------|
| EU RoHS Indicator | No |
| Grounding Style | 36 in Line Lead |
| Type | Underground Arresters |
| UPC | 096359695363 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 16.688 in x 9.250 in x 4.50 in |
| Height | 4.50 in |
| Length | 16.688 in |
| Weight | 9.4 lb |
| Width | 9.250 in |

Electrical Ratings

| | |
|---|--|
| Duty Cycle | 36 kV |
| MCOV | 29 kV |
| Maximum Discharge Voltage | <ul style="list-style-type: none">• 117.4 kV @ 1.5 kA• 100.5 kV @ 3 kA• 107.2 kV @ 5 kA• 120.7 kV @ 10 kA• 139.4 kV @ 20 kA• 174.3 kV @ 40 kA |
| Maximum Switching Surge Protective Level @ 500A | 84.5 kV |
| kV Class | 35 kV |

Logistics

| | |
|------------------|----|
| Pallet Quantity | 54 |
| Standard Package | 1 |

Product Assets

- [Catalogs - Cable Accessories \(C7\)](#)
- [Catalogs - Underground Arresters \(C6\)](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
- [Sales Drawings - 35 kV, 200A Large interface Loadbreak Elbow Arrester \(236ELA\)](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)
- [Video - Grease Best Practices \(HPS_CA_UTL_VI_EN_00030\)](#)