

Aluminum ADSS Suspension Clamp, Hanging, .751"-.825" Dia.

By Hubbell Power Systems
Catalog # HUBSUSH205



Hanging ADSS suspension clamp for .751"-.825" cable diameters.

Features

- Installation with J-hook or eye-bolt
- Tangent suspension for spans up to 600 ft.
- Meets IEEE 1591.2

Application

ADSS Cable Suspension

General

Bolt Installation Torque (Recommended)	180 in-lbs
Material - Bolt	Galvanized Steel
Material - Casting	Aluminum Alloy
Material - Washer	Galvanized steel/Neoprene
Product Category	Communications Connectors
UPC	096359665311

Dimensions

Dimensions	6.082 in x 2.486 in x 5.483 in
Height	5.483 in
Length	6.082 in
Weight	1.800 lb
Width	2.486 in

Logistics

Carton Quantity	10
Pallet Quantity	640

Product Assets

[Installation Manuals - Hanging Aluminum ADSS Suspension Clamp Instructions](#)
[Literature - Hanging AL ADSS Susp. Clamp \(SF05112E\)](#)
[Sales Drawings - HUBSUSHxxx Drawing](#)
[Video - Hubbell Power Systems Aluminum ADSS Suspension Clamp Installation \(VI05125E0818\)](#)

Related Products

[SVD106 - Spiral Vibration Damper, .563"-.760" O.D.](#)
[HUBSUSF205 - Aluminum ADSS Suspension Clamp, Fixed, .751"-.825" Dia.](#)