

15kV Fused Elbow, 0.720 - 0.985 Cable insulation dia range, Cooper Fuse Connector

By Hubbell Power Systems
Catalog # [215FECB3](#)

Fused Elbow, 15 kV, with Test Point, Cable Insulation Diameter range = 0.720 - 0.985 inches, #1 Solid or Compact and #2 Stranded or Compressed, Accepts Cooper Current Limiting Fuses



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Cooper Fuse Connector
Integral Seal	No
PROBELOK® Connectors	No
Type	200A Loadbreak
With Seal Kit	No
With Test Point	Yes

Dimensions

Cable Insulation Diameter Maximum	0.985 in
Cable Insulation Diameter Minimum	0.720 in
Weight	7.0 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.720 - 0.985
Solid or Compact Conductor	#1
Stranded or Compressed Conductor	#2

Logistics

Pallet Quantity	240
Standard Package	1

Product Assets

[Catalogs - Cable Accessories \(C7\)](#)
[Installation Manuals - IS200FE_-_Fused_Elbow_Installation_Instructions](#)
[Sales Drawings - 215FE Sales Drawing](#)
[Test Documents - 15kV Fused Elbow Test Report](#)
[Video - Grease Best PRactices \(HPS_CA_UTL_VI_EN_00030\)](#)